

2014-5825 2015-01-13
(BOX)

LENTEK

A World Leader in Electronic Pest Control Technology

Today's Answer to Rodent Control!

Pest Contro DELUXE

DOMESTIC

ULTRA-SONIC TECHNOLOGY

RAT AND MOUSE REPELLER

NO Sprays or Fumes

NO Messy Cleanup

READ LABEL AND INSTRUCTION MANUAL BEFORE USING

REG. NO. 27050 P.C.P. ACT

PROTECTS UP TO 232m²
(2500 sq. ft.)

PLUS Floor Light

- Rats
- Mice

PESTCONTRO DELUXE IS IDEAL FOR USE IN:

- HOMES**
- WAREHOUSES**
- OFFICE BUILDINGS**
- RESTAURANTS**
- GARAGES**
- SCHOOLS**
- CLUB HOUSES**
- APARTMENT BUILDINGS**
- BARNS/STABLESany large buildings!**

PKGCO2CAN-G-7A

For more information on Koolatron and our line of products:

Visit us on the web: www.koolatron.com TM

Canadian Customers : Koolatron, 139 Copernicus Blvd., Brantford, ON N3P 1N4

US Customers : Koolatron, 4330 Commerce Drive, Batavia, NY 14201

Site Web: www.koolatron.com

2005 Koolatron, Inc. All rights reserved

All specifications are subject to change without notice

For use with and in conjunction with normal control practices.

EPA EST NO. 79092-CHN-001 MADE IN CHINA

((See labelled illustration))

**NO MESSY SPRAYS AND TRAPS TO BUY.
NO EXPENSIVE PEST CONTROL SERVICES TO HIRE.
NO DEAD RODENTS TO DISPOSE OF.**

**Thank you for purchasing PestContro Deluxe!
Today's answer to rodent control.**

((BOOKLET))

PestContro® DELUXE

Instruction Manual

Rats

Mice

DOMESTIC

READ THE LABEL AND INSTRUCTION MANUAL BEFORE USING

REG. NO. 27050 P.C.P. ACT

KOOLATRON INC., 139 COPERNICUS BLVD., BRANTFORD ON N3P 1N4

LENTEK, A DIVISION OF KOOLATRON INC.

All specifications are subject to change without notice.
Dimensions are approximate.

by
LENTEK

DIRECTIONS FOR USE

Congratulations on your purchase of the PestContro Deluxe. You have purchased a quality product that has been thoroughly tested to meet the highest standards. Your complete satisfaction is important to us. Please read through the directions thoroughly and then enjoy

your PestContro Deluxe. Thank You!

Just plug PestContro Deluxe into a centrally located area unobstructed by furniture and other objects.

((See labelling and illustration))

Ultrasonic Sound Features

The PestContro Deluxe incorporates dual speakers that create a harsh ultrasonic siren, inaudible to humans. See commonly asked questions for additional information on ultrasonic sound.

1. Variable/Fixed Pitch Selector

In the variable setting, the two speakers sweep within a range of ultrasonic sound frequencies, like two squalling and conflicting sirens. If set to the FIXED setting the speakers broadcast a single tone. You may hear the difference by pushing the TEST button. Lentek recommends first setting to the FIXED setting and changing to VARIABLE if adequate results are not met.

2. Continuous/Random On-Off Selector

The Random On/Off Setting automatically turns each speaker on and off randomly to keep pests from becoming accustomed to the ultrasonic sounds. This mode will use 50% less electricity. In the continuous setting, both speakers broadcast continuously. Koolatron recommends first setting to the CONTINUOUS setting and changing to RANDOM ON-OFF if adequate results are not met.

3. Floor Night Light Switch

Switching the On/Off switch on the left side of the uni while plugged into an outlet, will turn on and off the Floor Night Light. Users enjoy this feature if PestContro Deluxe is placed in a hall or dimly lit area.

4. Test Button

When the PestContro Deluxe is plugged into a power outlet, pushing the test button will lower the ultrasonic frequencies to an audible human level. Pushing the test button will allow you to hear the different ultrasonic features. To avoid hearing damage, do not use the Test button for

long periods of time and do not allow children to play with the test switch.

LED's

Each LED represents different properties of PestContro Deluxe. The Red LED will continually flash. While the green LED's represent sound emitting from each of the speakers. The Green LED's will randomly turn on and off if set in VARIABLE setting, and will remain constantly on during other settings.

Power

The PestContro Deluxe is powered by a 110 volt outlet, or the represented power configuration indicated on the outside of the box. For worldwide applications, make sure you are using the correct plug configuration or the proper power converter that conforms to the local voltage and outlets. Contact your local dealer or Koolatron if you have a question concerning power issues.

Specification

Dimensions: 2.5cm x 8.5cm x 13.5cm

Power input: 100 - 120 V or 220 - 240 V

Safety standards: UL, CE

Power consumption: 15 watts

Coverage: 232 sq. m. (2500 sq. ft.) required one per floor

-Direct Plug-in

-LED status indicators

-Built-in night light

-Audible test button

-Twin dual ceramic piezo sirens Exclusive Pest Control Technology

-Ultrasonic Sound high/low band range selector

-Continuous/Random on-off selector

Suggestions for Best Results

1. Take special care not to leave doors, windows, basements, or garage doors open as new

rodents or pests may wander in briefly before they are affected and repelled by PestContro Deluxe.

2. Take special care not to leave human, animal or pet food supplies in open areas which can attract new rodents or pests before they can be affected by PestContro Deluxe.

3. Take special care not to carry in new rodents or pests when transferring food, supplies, grains, animal feed, etc. from outside supply areas into areas not being protected by PestContro Deluxe.

Commonly Asked Questions:

1. Has PestContro Deluxe met any government standards?

PestContro Deluxe is UL (Underwriters Laboratories) approved, and CE approved for European Distribution. PestContro products by Lentek have won several awards including the highly prestigious Smithfield innovation Award in the UK.

2. What type of pests will PestContro Deluxe repel?

PestContro Deluxe helps to control Rats and Mice.

3. Will PestContro Deluxe affect my pets?

PestContro Deluxe will not affect the common domestic pets such as DOGS, CATS, and FISH.

4. Does PestContro Deluxe have any affect on other electrical or battery operated equipment?

PestContro Deluxe does not affect any electrical appliance, equipment, or security systems. Battery operated equipment will not be affected since it is not physically connected to the unit.

5. Will PestContro Deluxe be less effective if doors or windows are opened?

The ultrasonic waves can be affected only by the physical nature of the home itself. Ultrasound can not penetrate solid objects like walls or doors. When PestContro Deluxe is placed in a closed room, the ultrasound would only be effective in that room. If a door is opened, the sound waves will be able to travel to other areas of the home. The waves reflect off of solid objects and can lose some effectiveness because of screened windows and doors. It is recommended a customer purchase additional units if they would like the ultrasonic sound effect in additional closed areas of the house.

6. How many units will I need for my home?

PestContro Deluxe was designed to cover up to a 232 sq. m. (2500 sq. ft.) home. It is necessary to purchase additional units if a home is greater than 232 sq. m. (2500 sq. ft.) or more than one floor. However, many people purchase additional single room ultrasonic units for added protection in attics, basements, crawl spaces, and other problem areas. PestContro Deluxe is also ideal for warehouses and other large buildings with pest problems.

7. Does the location of the unit have to be changed?

Koolatron recommends that the unit be placed in a central, unobstructed area. If favorable results are not obtained after the first 15 days, it is recommended to move the unit to another area of the home, possibly the area where pests are seen most often. Placing the unit in the living room or across from the kitchen cabinets proves to be an extremely effective location for ridding pests.

8. Does PestContro Deluxe affect pacemakers?

PestContro Deluxe has never been found to affect a pacemaker.

9. How long does it take for PestContro Deluxe to be effective?

Under normal conditions, for the first few days of use there should be an increase in visible activity of pests living within your home. This is known as the flushing out period. The pests will leave the unpleasant environment created by PestContro Deluxe, usually within 10-14 days. However, due to the 30 day gestation period of some pests, new pests may be seen after the 30 day period.

10. What is the estimated life of PestContro Deluxe?

Due to the solid construction and limited moving parts, PestContro Deluxe should offer 5 years of continuous use. The product is warranted for 2 years.

11. Does PestContro Deluxe ever need servicing or repair?

Under normal conditions, PestContro Deluxe requires no maintenance of any kind.

12. Will I be able to hear PestContro Deluxe?

The ultrasound frequency is set to be heard ONLY by rodents. It is possible you will hear a clicking sound in the random frequency.

13. Can PestContro Deluxe be plugged in using a power adapter or extension cord?

Yes.

14. How much electricity does PestContro Deluxe use?

Power consumption is minimal. PestContro Deluxe uses just pennies worth of electricity a day to operate. Tests have shown that PestContro Deluxe costs less to operate than a 40 watt light bulb.

WARRANTY

This KOOLATRON product is warranted to the retail customer for 90 days from date of retail purchase, against defects in material and work-manship.

WHAT IS COVERED

- Replacement parts and labour.
- Transportation charges to customer for the repaired product.

WHAT IS NOT COVERED

- Damage caused by abuse, accident, misuse, or neglect.
- Transportation of the unit or component from the customer to Koolatron.

IMPLIED WARRANTIES

Any implied warranties, including the implied warranty of merchantability are also limited to the duration of 90 days from the date of retail purchase.

WARRANTY REGISTRATION

Register on-line at www.koolatron.com AND keep the original, dated, sales receipt with this manual.

WARRANTY AND SERVICE PROCEDURE

If you have a problem with your PC02, or require replacement parts, please telephone the following number for assistance:

North America 1-800-265-8456

The Service Advisors will advise you on the best course of action.
Koolatron has Master Service Centres at these locations:

Koolatron U.S.A.
4330 Commerce Dr.
Batavia, NY 14020-4102 U.S.A.

Koolatron Canada
139 Copernicus Blvd.
Brantford, ON N3P 1N4 Canada

A Koolatron Master Service Centre must perform all warranty work.

This label transcript service is offered by the Pest Management Regulatory Agency to provide efficient searching for label information. This service and this information do not replace the official hard-copy label. The PMRA does not provide any guarantee or assurance that the information obtained through this service is accurate, current or correct, and is therefore not liable for any loss resulting, directly or indirectly, from reliance upon this service.