

2016-7281
2016-12-14

FRONT

Lentek™ PestContro®
ULTRASONIC PEST REPELLER
BATTERY-OPERATED & PORTABLE

PROTECTS UP TO 232m² (2500 sq.ft.)
POWERED BY 3 'AA' Batteries
FOR UP TO 4 MONTHS
Batteries not included.

TARGETS RODENT PESTS (RATS, MICE)
FOR INDOOR USE ONLY

NO Cords
NO Sprays
NO Fumes
NO Messy Cleanup

REG NO. 31743 P.C.P. ACT

TOP

- Targeting rodent pests (rats, mice)
- Portable ultrasonic pest repeller
 - Completely Portable
 - Automatic 120 dB Ultrasonic signal
 - Dual Ultrasonic Frequency
 - Features new Custom IC
 - LED Power Indicator light
 - Audible Test button
 - Power ON/OFF

DOMESTIC

READ THE LABEL AND MANUAL BEFORE USING
MANUAL INSIDE PACKAGE.

PMRA Approved carton, compared to own precedent. 2016-2526. JMT
Nov 2, 2016

KEEP OUT OF REACH OF CHILDREN

LEFT SIDE

www.koolatron.com
1.800.265.8456

Koolatron, Inc.
139 Copernicus Blvd.
Brantford, ON N3P 1N4
Canada

©2016 Koolatron, Inc. All rights reserved.
All specifications are subject to change without notice.

PR23-G

UPC barcode

Made in China

RIGHT SIDE

Lentek™ PestContro® BRAND
MILLIONS SOLD!!!

Can be used in home, office, shed or covered outbuilding, warehouses,
restaurants, garages, schools, cottages, apartment buildings, farm
buildings, private boats and RVs, domestic kennels and stables.

Lentek™ PestContro®
ULTRASONIC PEST REPELLER
BATTERY-OPERATED & PORTABLE

DOMESTIC
REG NO. 31743 P.C.P. ACT

PR23-G
Instruction Manual

SPECIFICATIONS

Dimensions: W 12 cm x D 5 cm x H 7.5 cm (W 4.75" x D 2" x H 3")

Power: Three (3) "AA" Batteries (Alkaline recommended)

Battery Life: Up to 4 months continuous operation

Safety: For Indoor Use Only

- do not place where it will come in contact with water


Coverage: 232m² (2500 sq.ft.), required one per floor

FEATURES

- Completely Portable – place wherever you need it to fight rodent infestations in your home, office, shed, enclosed porches or covered outbuilding
- Automatically emits a powerful 120 dB Ultrasonic signal for 2 full seconds with 1 second each of two frequencies specifically targeting rodent pests (rats, mice); repeats every 3 minutes.
- Dual Ultrasonic Frequency – automatically emits 1 second blasts at 40 kHz (+/- 10 kHz that target mice and rats.
- Features new Custom Integrated Circuit (IC) for best possible accuracy of the ultrasonic sirens emanating from the unit and better battery performance
- LED Power Indicator light and Audible Test button to assure ultrasonic function is working correctly
- Power ON/OFF slide switch
- Batteries Last up to 4 months!

- Can be used in home, office, shed or covered outbuilding, warehouses, restaurants, garages, schools, cottages, apartment buildings, farm buildings, private boats and RVs, domestic kennels and stables.

PARTS



BATTERY INSTALLATION

1. Remove Battery Cover on the back of the unit by pushing down on the tab and lifting out the cover.
2. Install three (3) "AA" Batteries (Alkaline recommended) making sure the positive and negative pole markings on the inside of the unit match up with the battery markings.
3. Replace Battery Cover by sliding the bottom into place first and then push down into its original sealed position.

HOW LONG WILL YOUR BATTERIES LAST?

Three "AA" Alkaline Batteries should last up to 4 months. Replace as needed, or when the Red LED Power Indicator light is no longer glowing.

TWO WAYS TO MAKE SURE YOUR NEW PRODUCT IS WORKING

1. Push the ON/OFF Slide Switch on the side of the unit to the ON position.
2. The RED LED light above the switch should glow red, indicating power is activated.

3. TEST the Ultrasonic sirens by pushing the TEST button on the top of the unit down for 3 seconds; you will hear a siren-like noise emitting from the front speakers. Depressing the TEST Button brings the Ultrasonic Sirens down to a human-audible level so we can confirm the product is working.

WARNING: Do not press down the TEST Button for an extended period.

HOW TO USE YOUR NEW PRODUCT

- Once powered on, two one-second Ultrasonic Siren bursts are emitted from the front speakers every three minutes. Each burst is at 40 kHz (+/- 10 kHz), a frequency range that is audible to rodents (rats, mice, squirrels) and other pests, but inaudible to humans, cats, dogs and birds.
- These Ultrasonic bursts are emitted at a powerful 120 dB level, loud enough to be a discomfort to unwanted rodent visitors, and discourage them from staying within earshot of your new Ultrasonic Rodent Repeller.
- Because this product is Battery Operated and does not require a plug, you can place it where you need it, aiming the Ultrasonic Sirens specifically at problem areas. You can move the unit from place to place as often as you like, and as needed.
- Your PestContro® Ultrasonic Device should be used in rooms where signs of mouse or rat activity is observed. Placement of the device is important. Ultrasonic waves travel in a straight line and bounce off non-absorbing materials to fill a room. Hard surfaces such as walls, doors, appliances, etc. will reflect the ultrasonic waves.

The area covered by the ultrasonic waves may be better when there are more reflective surfaces where the ultrasonic device is placed.

Ultrasound cannot penetrate through hard or solid objects. Rodents behind these types of objects will not be repelled. The portability of your new PestContro product allows you to freely and frequently move the unit so the ultrasound waves have access to those areas. Note that sound absorbing materials such as carpets, drapes and soft furniture will also reduce the ultrasonic range of the device. Ultrasound will be stronger near the device and in the room where the device is placed.

CAUTION! This product is intended for use Indoors only. To avoid risk of fire or electric shock, do not use where it may be exposed to water or direct sunlight.

PRECAUTIONS

- * Children should not play for extended periods in close proximity to the device(s).
- * Avoid contact exposure when the device is operating.
- * Limit extended exposure to a distance of 2m (6.6 ft.) from the device.
- * While the Ultrasonic Frequencies are above the hearing range of dogs, cats and birds, you should still not permit pets continuous exposure to the device.

WARRANTY

This product is warranted to the retail consumer for 90 days from date of retail purchase, against defects in material and workmanship.

WHAT IS COVERED

- Replacement parts and labor.
- Transportation charges to customer for the repaired product.

WHAT IS NOT COVERED

- Commercial or industrial use of this product.
- Damage caused by abuse, accident, misuse, or neglect.
- Transportation of the unit or component from the customer to a Master Service Centre.

IMPLIED WARRANTIES

Any implied warranties, including the implied warranty of merchantability are also limited to duration of 90 days from the date of retail purchase.

WARRANTY REGISTRATION

Register on-line at www.koolatron.com AND keep the original, dated, sales receipt with this manual.

WARRANTY AND SERVICE PROCEDURE

If you have a problem with your unit, or you require replacement parts, please telephone the following number for assistance: 1-800-265-8456

A Master Service Centre must perform all warranty work. Service after warranty may be obtained at a Master Service Centre or at an authorized service dealer. Purchase Receipt is required to establish warranty eligibility.

Master Service Centres at these locations:

U.S.A.
4330 Commerce Dr.
Batavia, NY 14020-4102 U.S.A.

Canada
139 Copernicus Blvd.
Brantford, ON N3P 1N4 Canada

www.koolatron.com
©2016 All rights reserved.
All specifications are subject to change without notice.

Made in China

H1S161
10/2016-v5 CDN