

97.01.02

WOOLSEY

VINELAST

734 BLUE

SKIN IRRITANT

EYE IRRITANT

GUARANTEE

CUPROUS OXIDE....40%
Copper (as elemental)

READ THE LABEL BEFORE USING

REGISTRATION NO. 21642

PEST CONTROL PRODUCTS ACT

FOR USE ON BOATS ONLY

COMMERCIAL

MARINE

DANGER POISON

NET CONTENTS 3.8 Litres

CAUTION!

KEEP OUT OF REACH OF CHILDREN.

FLAMMABLE.

See Over Cautions on Back Panel.

Kop-Coat, Inc.
Woolsey Division
Rockaway, NJ
07866
USA

KEEP OUT OF REACH OF CHILDREN

Handle with care and mix only in a closed container. Use only in well ventilated areas. When using do not eat, drink or smoke. Take a shower immediately after work. Wear freshly laundered clothes daily. Wash hands and face before eating, drinking, smoking and using the toilet. Store and wash all protective clothing separately from household laundry. Wash protective clothing in detergent and hot water before reuse.

NOTICE TO USER

This control product is to be used only in accordance with the directions on this label. It is an offense under the Pest Control Products Act to use a control product under unsafe conditions.

VINELAST ANTI-FOULING FINISH DIRECTIONS FOR USE

VINELAST is the sleek anti-fouling bottom paint for all power and sailing craft-wood, fibreglass, or metal. VINELAST provides a smooth racing-quality finish that maximizes hull speed while protecting against all fouling attachments, even in tropical waters. VINELAST is extremely durable, especially formulated to withstand frequent trailering, launching and beaching. VINELAST applies easily, dries overnight and protects your bottom for years with minimal annual maintenance. VINELAST is only for use on ships and boats.

PREPARATION: If previously painted with "Lumalast", "Vinelast", or "Super Vinelast" apply "Vinelast" directly after proper surface preparation of a thorough wet sanding and removal of all loose paint. Otherwise, completely remove all old finishes and prepare the bare surface as follows:

WOOD: Reef out old embrittled seam compound and prime routed seams (using "Vinelast" thinned 10% with Woolsey 719 "Vinelast" Solvent).

Apply 1 priming coat of "Vinelast" thinned 10% with 719 Solvent to ensure penetration. Finish with at least 2, preferably 3, coats of "Vinelast".

METAL: Prime aluminum or steel with Woolsey Epoxy System consisting of 652/651 Epoxy Primer carefully following directions for these special products. (Alternate system: Primer with 3 coats Woolsey 648/649 "MPF" Epoxy Primer.) Finish with at least 2, preferably 3, of "Vinelast".

FIBREGLASS: Scour and scrub with Woolsey "Shipmate" 625 Heavy Duty Fibreglass Cleaner or other strong abrasive agent. Rinse well with fresh water and allow to dry. Sand vigorously until all sheen on gel coat has been removed. Use 1/0 or No. 80 grit

production paper. Wipe with clean rag moistened with alcohol. Apply "Vinylast" direct or prime with 1 coat Woolsey 650/651 "MPF" Epoxy Primer. Finish with at least 2, preferably 3, coats of "Vinylast".

APPLICATION: MIX WELL BEFORE USING! Also stir occasionally during use.

THINNING: Normally not required for brush application, except when using as a primer coat. Use Woolsey 719 "Vinylast" Solvent to clean brushes and equipment.

COVERAGE: 37 sq. metres per 3.8 litres for the first coat on new wood or repaint wood. 42 sq. metres per 3.8 litres on fibreglass and primed metal.

NUMBER OF COATS: At least 2, preferably 3, coats on original application. Thereafter, maintain annually with one heavy coat preceded by thorough wet sanding. Allow at least 4 hours drying time between coats. If desired, final coat may be burnished for racing.

LAUNCHING: Allow at least an overnight dry before launching. When an Epoxy Primer is used, allow a full 72 hours before launching.

Large vessels (i.e. over 25m) must be treated by trained applicators.

SELLER'S GUARANTEE SHALL BE LIMITED TO THE TERMS SET OUT ON THE LABEL AND SUBJECT THERETO. THE BUYER ASSUMES THE RISK TO PERSONS OR PROPERTY ARISING FROM THE USE OR HANDLING OF THIS PRODUCT AND ACCEPTS THE PRODUCT ON THAT CONDITION.

CAUTION

Keep away from heat, sparks and flame. Vapours heavier than air cause health and explosion hazards. Keep containers tightly closed when not in use. Avoid contact with eyes, skin and clothing. Do not breath vapours. USE AN AIR-FED RESPIRATOR WITH FULL FACE MASK DURING HANDLING AND APPLYING. WEAR CHEMICAL RESISTANT GLOVES AND FOOT WEAR AND CHEMICAL RESISTANT CLOTHING AT ALL TIMES DURING HANDLING AND APPLYING.

FIRST AID

IF SWALLOWED: Drink promptly a large quantity of milk, egg white, gelatin solution or, if these are not available, drink large quantities of water. Avoid alcohol. Get medical attention.

IF IN EYES: Flush with plenty of water. Get medical attention.

IF ON SKIN: Wash with plenty of soap and water. Get medical

attention. If not breathing, give artificial respiration, preferably mouth-to-mouth. Get medical attention.

ENVIRONMENTAL HAZARDS

Toxic to aquatic organisms. Do not contaminate water. Do not apply directly to water by cleaning equipment or disposal of wastes. Do not allow chips or dust generated during paint removal to enter water.

DISPOSAL

Dispose of empty containers and paint debris in accordance with provincial requirements. For information on the disposal of unused or unwanted product and the cleanup of spills, contact the Provincial Regulatory Agency or the manufacturer.

PHYSICAL OR CHEMICAL HAZARD:

FLAMMABLE! Do not use or store near heat or open flame.

This label transcript service is offered by the Pest Management Regulatory Agency to provide efficient searching for label information. This service and this information do not replace the official hard-copy label. The PMRA does not provide any guarantee or assurance that the information obtained through this service is accurate, current or correct, and is therefore not liable for any loss resulting, directly or indirectly, from reliance upon this service.

+))